

DAS 8930 Built-in ventilation hood with intuitive SmartControl White controls for use in narrow upper cabinets



- Intricate design flat stainless-steel panel, 36 in (90 cm)wide
- Unique user convenience Con@ctivity
- LED strip for uniform lighting
- Efficient filtration- 10-ply stainless steel grease filters
- Recirculation mode Active AirClean or Longlife AirClean filter

EAN: 4002516495628 / Material number: 11878590 / Old Material Number: 28S8930SUSA

•
Stainless steel
Can be retrofitted
DUU 151
DKF 31-P, DKF 31-R
•
Con@ctivity 3.0
•
•
•
1
•
•
•
•
2
•
1 x 3 W
270 lx
3500 Kelvin
•
•
•
418
•
34 (861)
2 3/8 (60)
12 1/8 (307)
24 1/8 (610)
24 1/8 (610) 42 (19.0)
24 1/8 (610) 42 (19.0) 2 (0.8)
42 (19.0)
42 (19.0) 2 (0.8)
42 (19.0) 2 (0.8)
42 (19.0) 2 (0.8)
42 (19.0) 2 (0.8) • 26 (660)
42 (19.0) 2 (0.8) • 26 (660)
42 (19.0) 2 (0.8) • 26 (660) 0.35 120



DAS 8930 Built-in ventilation hood with intuitive SmartControl White controls for use in narrow upper cabinets





EAN: 4002516495628 / Material number: 11878590 / Old Material Number: 28S8930SUSA

Installation note	
Vent connection at top	•
Vent connection at top and rear	•
Installation template	•
Standard accessories	
Non-return flap	•




DAS 8930 Built-in ventilation hood with intuitive SmartControl White controls for use in narrow upper cabinets





DAS8930, Installation drawings

1) Extraction, recirculation with conversion kit DUU 150., 2) Alternative ducting connection to the rear., 3) Accessory DSM module., 4) The wall unit can be fitted with a partition after installation. The slots for the grease filters and, in recirculation mode, for the odor filters must remain accessible., , The height of the wall unit and the cut-out dimensions must take into account any accessories fitted (e.g. silencer, recirculation hood conversion kit, DSM module)



DAS8930, drawing - US

1) Exhaust air, recirculation with DUU 150 conversion kit., 2) Exhaust air connection alternatively to the rear., 3) DSM module accessory., 4) The wall unit can be fitted with a partition after installation. The slots for the grease filters and, in the case of recirculation mode, for the odor filters must remain accessible. , , Mounted accessories must be taken into account for the cabinet height and cut-out dimensions (e.g. silencer, recirculation air conversion kit, DSM module).