## **LG REFRIGERATION**

# **LFDS22520S**

21.8 cu.ft. 3-Door French Door Refrigerator

21.8 cu.ft.

4 Split Shelves in Refrigerator

7 Total Door Bins

Smart Cooling® System

Multi-Air Flow™ Technology

2-Tier Organization in Freezer

**ENERGY STAR® Qualified** 

Inverter Linear Compressor with 10-Year Warranty

SmartDiagnosis™

Available in Stainless Steel



CAPACITY	
Refrigerator (cu.ft.)	14.5
Freezer (cu.ft.)	7.3
Total (cu.ft.)	21.8
FEATURES	
Energy Consumption (kWh/Year)	587
ENERGY STAR® Qualified	Yes
WATER & ICE SYSTEM	
Water Dispenser	Yes
Daily Ice Production (lbs)	2.8
IcePlus™ Production (lbs)	3.1
Ice Storage Capacity (lbs)	12.0
Ice System	Factory Installed Ice Maker
Dispenser Light	Yes
Water Filter	LT700P
COOLING	
Linear Compressor	Yes
Smart Cooling® System	Yes
Multi-Air Flow	Yes
Temperature Sensors	4
CONVENIENCE	
Display Type	Membrane / White LED
Temperature Controls	Electronic/Digital
Door Alarm	Yes
Child Lock	Yes
ADA Compliant	Yes
LoDecibel™ Quiet Operation	Yes
REFRIGERATOR	
No. of Shelves	4 Split
Cantilevered Shelves	Hybrid Cantilevered
Shelf Construction	Spill Protector™ Tempered Glass
Crisper Bins	2 Humidity Crispers
Glide N' Serve® Drawer	Yes
Refrigerator Light	Ceiling LED
REFRIGERATOR DOOR	
No. of Bins	7 Total (5 Gallon Sized, 2 Half)
Door Bin Construction	2 Pieces (Clear + Opaque)
FREEZER	

Door Type	Pull Drawer
Drawers	2-Tier Organization
DuraBase™ Solid Drawer Base	Yes
Drawer Divider	Yes
Ice Bin / In-Door Ice	Icemaker & Ice bin in the freezer
Freezer Light	Ceiling LED
Freezer Handle	Vista
SMARTTHINQ®	
SmartDiagnosis™	Yes
MATERIALS AND FINISHES	
Contour Door	Yes
Hidden Hinges	Yes
Surface	Smooth
Handles	Matching Commercial Handles
All Available Colors	Stainless Steel
DIMENSIONS/CLEARANCES/WEIGHTS	
Depth with Handles	35 1/2"
Depth without Handles	33"
Depth without Door	29"
Depth (Total with Door Open)	44 3/4"
Height to Top of Case	67 1/4"
Height to Top of Door Hinge	68 1/2"
Width	29 3/4"
Width (Door Open 90° with Handle)	38 1/4"
Width (Door Open 90° without Handle)	33 1/4"
Door Edge Clearance with Handle	4 1/2"
Door Edge Clearance without Handle	2"
Installation Clearance	Sides 1/8", Top 1", Back 2"
Weight (Unit/Carton)	237 lbs. / 259 lbs.
Carton Dimensions (WxHxD)	31 1/2" x 69 3/8" x 37 3/4"
LIMITED WARRANTY	
Parts & Labor	1 Year
Sealed System	7 Years
Linear Compressor	10 Years
UPC CODES	
LFDS22520S (Stainless Steel)	048231795098

## **LG REFRIGERATION**

## **LFDS22520S**

21.8 cu.ft. 3-Door French Door Refrigerator

### **QUICK INSTALL & CLEARANCES**

## For full installation directions/clearances please refer to the corresponding User Manual and Installation Guide.

DIMENSIONS/CLEARANCES/WEIGHTS	
A Depth without Handles	33"
B Width	29 3/4"
C Height to Top of Case	67 1/4"
D Height to Top of Door Hinge	68 1/2"
E Back Clearance	2"
F Depth without Door	29"
G Depth (Total with Door Open)	44 3/4"
M Depth with Handles	35 1/2"
Width (Door Open 90° with Handle)	38 1/4"
Width (Door Open 90° without Handle)	33 1/4"
Door Edge Clearance with Handle	4 1/2"
Door Edge Clearance without Handle	2"
Installation Clearance	Sides 1/8", Top 1", Back 2"
Carton Dimensions (WxHxD)	31 1/2" x 69 3/8" x 37 3/4"

#### CHOOSING THE PROPER LOCATION

#### WATER

Select a place where a water supply can be easily connected for the automatic

#### NOTE

The water pressure must be 20 – 120 psi or 138 – 827 kPa or 1.4 – 8.4 kgf/cm². If the
refrigerator is installed in an area with low water pressure (below 20 psi), you can install a
booster pump to compensate for the low pressure.

#### **ELECTRICITY**

The refrigerator should always be plugged into its own individual properly grounded electrical outlet rated for 115 Volts, 60 Hz, AC only, and fused at 15 or 20 amperes. This provides the best performance and also prevents overloading house wiring circuits which could cause a fire hazard from overheated wires. It is recommended that a separate circuit serving only this appliance be provided.

#### WARNING

To reduce the risk of electric shock, do not install the refrigerator in a wet or damp area.

#### FLOORING

To avoid noise and vibration, the unit must be leveled and installed on a solidly constructed floor. If required, adjust the leveling legs to compensate for the unevenness of the floor. The front should be slightly higher than the rear to aid in door closing. Leveling legs can be turned easily by tipping the cabinet slightly. Turn the leveling legs to the left to raise the unit or to the right to lower it.

#### NOTE

 Installing on carpeting, soft tile surfaces, a platform or weakly supported structure is not recommended.

#### AMBIENT TEMPERATURE


Install this appliance in an area where the temperature is between 55°F (13°C) and 110°F (43°C). If the temperature around the appliance is too low or high, cooling ability may be adversely affected.












#### CONNECTING POWER AND SECURING SPACE FOR WATER SUPPLY PIPE

 $oldsymbol{\Lambda}$  Make sure the location of the water supply pipe is within the marked range.

Before connecting the power, always make sure to ground the product. (If the product is not grounded, the user may be able to feel the electricity due to the minute leakage current when touching the refrigerator door handle or side corner even when there is no issue with the product.)


▲ Do not ground the product to gas pipe, plastic water pipe or telephone wire etc. It can cause electric shock and explosion.



#### Power connection

The location of the 115V 60Hz power connector must be located on the rear side of the product as shown in the picture.

When installing the product, make sure to check whether the cord is hung on the hook on the rear side so that it is not pressed on the refrigerator. Damaged power cord can cause a fire.



Installation space for water supply pipe

Place the water hose for ice maker and water dispenser as shown in the picture, and prepare hose to come up from the floor (Copper pipe with diameter of 5/16"(8mm) is recommended for the water hose.) If the water pipe and water hose is located far from the product, bury the water hose on the floor and provide appropriate treatment.